

PRODUCT INFORMATION PACKET



Model No: E482
Catalog No: E482
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	15.0 Hp
Output KW	11.2 kW	Voltage	230/460 V
Speed	1725 r/min	Service Factor	1.15
Frame	D254JM	Enclosure	Drip Proof
Ambient Temperature	40 °C	Frequency	60 Hz
Current	39.6/19.8 A	Duty	Continuous
Insulation Class	F	UL	Recognized
CSA	Y		

Technical Specifications

Poles	4	Rotation	Reversible Counterclockwise
Drive End Bearing	309sf	Opp Drive End Bearing	206sf
Frame Length	12.50 in		
Connection Drawing	80022802.PCX		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025