

# PRODUCT INFORMATION PACKET



Model No: E483  
Catalog No: E483  
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	15.0 Hp
Output KW	11.2 kW	Voltage	230/460 V
Speed	1725 r/min	Service Factor	1.15
Frame	D254JP	Enclosure	Drip Proof
Ambient Temperature	40 °C	Frequency	60 Hz
Current	39.6/19.8 A	Duty	Continuous
Insulation Class	F	UL	Recognized
CSA	Y		

**Technical Specifications**

Poles	4	Rotation	Reversible Counterclockwise
Drive End Bearing	309sf	Opp Drive End Bearing	206sf
Frame Length	12.50 in		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025