



**Nameplate Specifications**

Phase	3	Output HP	20.0 Hp
Output KW	14.9 kW	Voltage	230/460 V
Speed	3505 r/min	Service Factor	1.15
Frame	S254JP	Enclosure	Drip Proof
Ambient Temperature	40 °C	Frequency	60 Hz
Current	51.0/25.5 A	Duty	Continuous
Insulation Class	F	UL	Recognized
CSA	Y		

**Technical Specifications**

Poles	2	Rotation	Reversible
Drive End Bearing	309sf	Opp Drive End Bearing	207sf
Frame Length	13.00 in		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025