

# PRODUCT INFORMATION PACKET



Model No: E5004  
Catalog No: E5004  
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	30.0 Hp
Output KW	22.4 kW	Voltage	230/460 V
Speed	1760 r/min	Service Factor	1.15
Frame	S286TC	Enclosure	Drip Proof
Ambient Temperature	40 °C	Frequency	60 Hz
Current	75.0/37.5 A	Duty	Continuous
Insulation Class	F	UL	Recognized
CSA	Y		

**Technical Specifications**

Poles	4	Rotation	Counterclockwise
Frame Length	14.00 in		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025