

PRODUCT INFORMATION PACKET



Model No: E587
Catalog No: E587
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Phase	3	Output HP	20.0 Hp
Output KW	14.9 kW	Voltage	230/460 V
Speed	1175 r/min	Service Factor	1.15
Frame	286T	Enclosure	Drip Proof
Efficiency	93 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	52/26 A
Duty	Continuous	Insulation Class	F
CSA	Y		

Technical Specifications

Poles	6	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	311sf
Opp Drive End Bearing	210sf	Frame Length	9.50 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025