



Nameplate Specifications

| | | | |
|------------|-------------------|---------------------|-------------------|
| Phase | 3 | Output HP | 30.0 Hp |
| Output KW | 22.4 kW | Voltage | 575 V |
| Speed | 1760 r/min | Service Factor | 1.15 |
| Frame | S286T | Enclosure | Drip Proof |
| Efficiency | 92.4 % | Ambient Temperature | 40 °C |
| Frequency | 60 Hz | Current | 30 A |
| Duty | Continuous | Insulation Class | F |
| UL | Recognized | CSA | Y |

Technical Specifications

| | | | |
|-------------------|-----------------|-----------------------|------------------------------------|
| Poles | 4 | Rotation | Reversible Counterclockwise |
| Drive End Bearing | 311sf | Opp Drive End Bearing | 207sf |
| Frame Length | 14.00 in | | |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025