



Nameplate Specifications

Phase	3	Output HP	40.0 Hp
Output KW	29.8 kW	Voltage	230/460 V
Speed	1780 r/min	Service Factor	1.15
Frame	324T	Efficiency	93 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	95/47.5 A	Duty	Continuous
Insulation Class	F		

Technical Specifications

Rotation	Reversible Counterclockwise	Drive End Bearing	6312
Opp Drive End Bearing	6312		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025