

**Nameplate Specifications**

Phase	3	Output HP	40.0 Hp
Output KW	29.8 kW	Voltage	230/460 V
Speed	1780 r/min	Service Factor	1.15
Frame	324T	Enclosure	Drip Proof
Efficiency	94.1 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	96.0/48.0 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

**Technical Specifications**

Poles	4	Rotation	Reversible Counterclockwise
Mounting	Rigid Base	Drive End Bearing	312s
Opp Drive End Bearing	312s	Frame Length	0.00 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025