

**Nameplate Specifications**

Phase	3	Output HP	50.0 Hp
Output KW	37.3 kW	Voltage	230/460 V
Speed	1785 r/min	Service Factor	1.15
Frame	326T	Enclosure	Drip Proof
Efficiency	94.5 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	120.0/60.0 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	4	Rotation	Reversible Counterclockwise
Mounting	Rigid Base	Drive End Bearing	312s
Opp Drive End Bearing	312s	Frame Length	0.00 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025