

**Nameplate Specifications**

| | | | |
|--------------------|---------------|---------------------|-----------------------------|
| Phase | 3 | Output HP | 50.0 Hp |
| Output KW | 37.3 kW | Voltage | 575 V |
| Speed | 1775 r/min | Service Factor | 1.15 |
| Frame | 326T | Enclosure | Totally Enclosed Fan Cooled |
| Thermal Protection | No Protection | Ambient Temperature | 40 °C |
| Frequency | 60 Hz | Current | 46.0 A |
| Duty | Continuous | Insulation Class | F |
| UL | Recognized | CSA | Y |
| Number of Speeds | 1 | | |

Technical Specifications

| | | | |
|-------------------|------------|-----------------------|------------|
| Rotation | Reversible | Mounting | Rigid Base |
| Drive End Bearing | Ball | Opp Drive End Bearing | Ball |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025