

PRODUCT INFORMATION PACKET



Model No: E767
Catalog No: E767
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Phase	3	Output HP	75 Hp
Output KW	56.0 kW	Voltage	575 V
Speed	1785 r/min	Service Factor	1.15
Frame	365T	Efficiency	94.1 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	69 A	Duty	Continuous
Insulation Class	F		

Technical Specifications

Rotation	Reversible Counterclockwise	Drive End Bearing	6314
Opp Drive End Bearing	6312		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025