

PRODUCT INFORMATION PACKET



Model No: E936
Catalog No: E936
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	125 Hp
Output KW	93.3 kW	Voltage	575 V
Speed	1790 r/min	Service Factor	1.15
Frame	405T	Efficiency	95.4 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	115 A	Duty	Continuous
Insulation Class	F		

Technical Specifications

Rotation	Reversible Counterclockwise	Drive End Bearing	6317
Opp Drive End Bearing	6313		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025