

PRODUCT INFORMATION PACKET



Model No: K222
Catalog No: K222
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	1	Output HP	3.0 Hp
Output KW	2.2 kW	Voltage	115/230 V
Speed	3500 r/min	Service Factor	1
Frame	H184T	Enclosure	Totally Enclosed Non Ventilated
Efficiency	75.5 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	30/15 A
Duty	Continuous	Insulation Class	B
UL	Recognized	CSA	Y

Technical Specifications

Poles	2	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	206
Opp Drive End Bearing	204	Frame Length	9.75 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025