

**Nameplate Specifications**

Phase	3	Output HP	7.5 Hp
Output KW	5.6 kW	Voltage	230/460 V
Speed	3490 r/min	Service Factor	1.15
Frame	Y184T	Enclosure	Drip Proof
Efficiency	90.2 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	17.2/8.60 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

**Technical Specifications**

Poles	2	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	206
Opp Drive End Bearing	204	Frame Length	10.75 in
Connection Drawing	80022802.PCX		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025