

**Nameplate Specifications**

Phase	3	Output HP	2.0 Hp
Output KW	1.5 kW	Voltage	230/460 V
Speed	1180 r/min	Service Factor	1.15
Frame	E184T	Enclosure	Drip Proof
Efficiency	87 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	7.4/3.7 A
Duty	Continuous	Insulation Class	F
CSA	Y		

Technical Specifications

Poles	6	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	206
Opp Drive End Bearing	204	Frame Length	9.25 in
Connection Drawing	80022802.PCX		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025