

**Nameplate Specifications**

Phase	3	Output HP	5.0 Hp
Output KW	3.7 kW	Voltage	230/460 V
Speed	3490 r/min	Service Factor	1.15
Frame	S182T	Enclosure	Drip Proof
Efficiency	85.5 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	12.4/6.2 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	2	Rotation	Counterclockwise
Drive End Bearing	206sf	Opp Drive End Bearing	204sf
Frame Length	9.00 in		
Connection Drawing	80022802.PCX		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025