

PRODUCT INFORMATION PACKET



Model No: E254V1
Catalog No: E254V1
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	3.0 Hp
Output KW	2.2 kW	Voltage	575 V
Speed	1760 r/min	Service Factor	1.15
Frame	182T	Efficiency	89.5 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	3.2 A	Duty	Continuous
Insulation Class	F		

Technical Specifications

Rotation	Reversible	Drive End Bearing	206
Opp Drive End Bearing	206		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025