

PRODUCT INFORMATION PACKET



Model No: E276
Catalog No: E276
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Phase	3	Output HP	3.0 2.2KW Hp
Voltage	200-230/460 V	Speed	1740 r/min
Service Factor	1.15	Frame	S182TCZ
Enclosure	Drip Proof	Efficiency	84 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	9.2-8.6/4.3 A	Duty	Continuous
Insulation Class	B	CSA	Y

Technical Specifications

Poles	4	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	207
Opp Drive End Bearing	204	Frame Length	7.75 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025