

# PRODUCT INFORMATION PACKET



Model No: E279  
Catalog No: E279  
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	5.0 3.7KW Hp
Voltage	200-230/460 V	Speed	3500 r/min
Frame	E182TCZ	Enclosure	Drip Proof
Efficiency	80 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	14.2-13/6.5 A
Duty	Continuous	Insulation Class	B
CSA	Y		

**Technical Specifications**

Poles	2	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	207sf
Opp Drive End Bearing	204sf	Frame Length	9.25 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025