

# PRODUCT INFORMATION PACKET



Model No: E282M  
Catalog No: E282M  
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	5.0 Hp
Output KW	3.7 kW	Voltage	230/460 V
Speed	1745 r/min	Service Factor	1.15
Frame	S184JM	Enclosure	Drip Proof
Ambient Temperature	40 °C	Frequency	60 Hz
Current	15/7.5 A	Duty	Continuous
Insulation Class	F	UL	Recognized
CSA	Y		

**Technical Specifications**

Poles	4	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	Ball Brg
Frame Length	7.75 in		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025