

# PRODUCT INFORMATION PACKET



Model No: E283  
Catalog No: E283  
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	5.0 Hp
Output KW	3.7 kW	Voltage	208-230/460 V
Speed	1740 r/min	Service Factor	1.15
Frame	S184JP	Efficiency	82.5 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	15-13.6/6.8 A	Duty	Continuous
Insulation Class	B		

**Technical Specifications**

Rotation	Reversible	Drive End Bearing	207
Opp Drive End Bearing	206		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025