

# PRODUCT INFORMATION PACKET



Model No: E285M  
Catalog No: E285M  
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	7.5 5.6KW Hp
Voltage	200-230/460 V	Speed	3500 r/min
Service Factor	1.15	Frame	H184JM
Enclosure	Drip Proof	Efficiency	82 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	21.8-20/10.0 A	Duty	Continuous
Insulation Class	F	CSA	Y

**Technical Specifications**

Poles	2	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	207
Opp Drive End Bearing	204	Frame Length	9.75 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025