

PRODUCT INFORMATION PACKET



Model No: E287M
Catalog No: E287M
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	7.5 Hp
Output KW	5.6 kW	Voltage	230/460 V
Speed	3490 r/min	Service Factor	1.15
Frame	M184TCZ	Enclosure	Drip Proof
Ambient Temperature	40 °C	Frequency	60 Hz
Current	17.2/8.6 A	Duty	Continuous
Insulation Class	F	UL	Recognized
CSA	Y		

Technical Specifications

Poles	2	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	Ball Brg
Frame Length	10.50 in		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025