

**Nameplate Specifications**

Phase	3	Output HP	10.0 Hp
Output KW	7.5 kW	Voltage	230/460 V
Speed	1740 r/min	Service Factor	1.15
Frame	S215TC	Enclosure	Drip Proof
Ambient Temperature	40 °C	Frequency	60 Hz
Current	25.8/12.9 A	Duty	Continuous
Insulation Class	F	UL	Recognized
CSA	Y		

**Technical Specifications**

Poles	4	Rotation	Counterclockwise
Frame Length	11.00 in		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025