

**Nameplate Specifications**

| | | | |
|--------------------|---------------|---------------------|-----------------------------|
| Phase | 3 | Output HP | 10.0 Hp |
| Output KW | 7.5 kW | Voltage | 230/460 V |
| Speed | 1745 r/min | Service Factor | 1.15 |
| Frame | 215TC | Enclosure | Totally Enclosed Fan Cooled |
| Thermal Protection | No Protection | Ambient Temperature | 40 °C |
| Frequency | 60 Hz | Current | 24.0/12.0 A |
| Duty | Continuous | Insulation Class | F |
| UL | Recognized | CSA | Y |
| Number of Speeds | 1 | | |

Technical Specifications

| | | | |
|-------------------|------------|-----------------------|-------|
| Rotation | Reversible | Mounting | Round |
| Drive End Bearing | Ball | Opp Drive End Bearing | Ball |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025