



Nameplate Specifications

Phase	3	Output HP	5.0 Hp
Output KW	3.7 kW	Voltage	230/460 V
Speed	3490 r/min	Service Factor	1.15
Frame	184TC	Efficiency	87.5 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	12/6 A	Duty	Continuous
Insulation Class	F		

Technical Specifications

Rotation	Reversible	Drive End Bearing	206
Opp Drive End Bearing	206		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025