

**Nameplate Specifications**

Phase	3	Output HP	25.0 Hp
Output KW	18.7 kW	Voltage	230/460 V
Speed	3545 r/min	Service Factor	1.15
Frame	284TSC	Efficiency	91 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	54.0/27.0 A	Duty	Continuous
Insulation Class	F		

**Technical Specifications**

Rotation	Reversible	Drive End Bearing	311
Opp Drive End Bearing	309		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025