



Nameplate Specifications

Phase	3	Output HP	30.0 Hp
Output KW	22.4 kW	Voltage	230/460 V
Speed	3530 r/min	Service Factor	1.15
Frame	286TSC	Efficiency	91 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	66/33 A	Duty	Continuous
Insulation Class	F		

Technical Specifications

Rotation	Reversible	Drive End Bearing	311
Opp Drive End Bearing	309		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025