



Nameplate Specifications

| | | | |
|------------|-------------------|---------------------|-------------------|
| Phase | 3 | Output HP | 10.0 Hp |
| Output KW | 7.5 kW | Voltage | 200 V |
| Speed | 1755 r/min | Service Factor | 1.15 |
| Frame | S215T | Enclosure | Drip Proof |
| Efficiency | 91.7 % | Ambient Temperature | 40 °C |
| Frequency | 60 Hz | Current | 29.0 A |
| Duty | Continuous | Insulation Class | F |
| UL | Recognized | CSA | Y |

Technical Specifications

| | | | |
|-------------------|-----------------|-----------------------|-------------------------|
| Poles | 4 | Rotation | Counterclockwise |
| Drive End Bearing | 208sf | Opp Drive End Bearing | 206sf |
| Frame Length | 11.00 in | | |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025