



### Nameplate Specifications

Phase	3	Output HP	7.5 Hp
Output KW	5.6 kW	Voltage	230/460 V
Speed	1760 r/min	Service Factor	1.15
Frame	213T	Efficiency	91.7 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	18/9 A	Duty	Continuous
Insulation Class	F		

### Technical Specifications

Rotation	Reversible	Drive End Bearing	208
Opp Drive End Bearing	207		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025