

PRODUCT INFORMATION PACKET



Model No: E355V1
Catalog No: E355V1
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	10.0 Hp
Output KW	7.5 kW	Voltage	575 V
Speed	1760 r/min	Service Factor	1.15
Frame	215T	Efficiency	91.7 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	9.6 A	Duty	Continuous
Insulation Class	F		

Technical Specifications

Rotation	Reversible	Drive End Bearing	208
Opp Drive End Bearing	207		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025