

# PRODUCT INFORMATION PACKET



Model No: E367  
Catalog No: E367  
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	10.0 Hp
Output KW	7.5 kW	Voltage	575 V
Speed	3495 r/min	Service Factor	1.15
Frame	215T	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Frequency	60 Hz	Current	9.2 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y
Number of Speeds	1		

**Technical Specifications**

Rotation	Reversible	Mounting	Rigid Base
Drive End Bearing	Ball	Opp Drive End Bearing	Ball

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025