

**Nameplate Specifications**

| | | | |
|---------------------|---------------|------------|--------------|
| Phase | 3 | Output HP | 7.5 5.6KW Hp |
| Voltage | 200-230/460 V | Speed | 1760 r/min |
| Service Factor | 1.15 | Frame | S213TCZ |
| Enclosure | Drip Proof | Efficiency | 87.5 % |
| Ambient Temperature | 40 °C | Frequency | 60 Hz |
| Current | 22-21/10.5 A | Duty | Continuous |
| Insulation Class | F | CSA | Y |

Technical Specifications

| | | | |
|-----------------------|------------|-------------------|------------|
| Poles | 4 | Rotation | Reversible |
| Mounting | Rigid Base | Drive End Bearing | 310 |
| Opp Drive End Bearing | 206 | Frame Length | 9.60 in |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025