



Nameplate Specifications

Phase	3	Output HP	10.0 7.5KW Hp
Voltage	200-230/460 V	Speed	3500 r/min
Service Factor	1.15	Frame	D213JM
Enclosure	Drip Proof	Efficiency	88.5 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	29-27/13.5 A	Duty	Continuous
Insulation Class	F	CSA	Y

Technical Specifications

Poles	2	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	310
Opp Drive End Bearing	206	Frame Length	10.60 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025