

**Nameplate Specifications**

Phase	3	Output HP	10.0 Hp
Output KW	7.5 kW	Voltage	230/460 V
Speed	3520 r/min	Service Factor	1.15
Frame	D213JP	Enclosure	Drip Proof
Ambient Temperature	40 °C	Frequency	60 Hz
Current	27/13.5 A	Duty	Continuous
Insulation Class	F	UL	Recognized
CSA	Y		

Technical Specifications

Poles	2	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	Ball Brg
Frame Length	10.60 in		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025