

**Nameplate Specifications**

Phase	3	Output HP	20.0 Hp
Output KW	14.9 kW	Voltage	230/460 V
Speed	1745 r/min	Service Factor	1.15
Frame	S256TC	Enclosure	Drip Proof
Efficiency	91 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	49.6/24.8 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	4	Rotation	Counterclockwise
Drive End Bearing	309sf	Opp Drive End Bearing	207sf
Frame Length	13.00 in		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025