

# PRODUCT INFORMATION PACKET



Model No: E4123  
Catalog No: E4123  
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	400 Hp
Output KW	298.4 kW	Voltage	460 V
Speed	1790 r/min	Service Factor	1
Frame	449T	Enclosure	Totally Enclosed Non Ventilated
Efficiency	96.2 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	443 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

**Technical Specifications**

Poles	4	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	6319
Opp Drive End Bearing	6318	Frame Length	0.00 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025