

PRODUCT INFORMATION PACKET



Model No: E576
Catalog No: E576
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Phase	3	Output HP	40.0 30.0KW Hp
Output KW	2267.8 kW	Voltage	200-230/460 V
Speed	3525 r/min	Service Factor	1.15
Frame	S286JP	Enclosure	Drip Proof
Efficiency	91 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	104-90/45 A
Duty	Continuous	Insulation Class	F

Technical Specifications

Poles	2	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	313
Opp Drive End Bearing	210	Frame Length	16.58 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025