

PRODUCT INFORMATION PACKET



Model No: E594
Catalog No: E594
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	25.0 Hp
Output KW	18.7 kW	Voltage	575 V
Speed	1740 r/min	Service Factor	1.15
Frame	S284T	Enclosure	Drip Proof
Efficiency	91.7 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	24.3 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	4	Rotation	Counterclockwise
Drive End Bearing	311	Opp Drive End Bearing	207
Frame Length	14.00 in		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025