

PRODUCT INFORMATION PACKET



Model No: E628V2
Catalog No: E628V2
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	40.0 Hp
Output KW	29.8 kW	Voltage	230/460 V
Speed	1780 r/min	Service Factor	1.15
Frame	324T	Efficiency	94.1 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	96/48 A	Duty	Continuous
Insulation Class	F		

Technical Specifications

Rotation	Reversible Counterclockwise	Drive End Bearing	6313
Opp Drive End Bearing	6311		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025