

**Nameplate Specifications**

Phase	3	Output HP	60 Hp
Output KW	44.8 kW	Voltage	230/460 V
Speed	3550 r/min	Service Factor	1.15
Frame	326TS	Efficiency	93.6 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	138/69 A	Duty	Continuous
Insulation Class	F		

**Technical Specifications**

Rotation	Reversible Counterclockwise	Drive End Bearing	6312
Opp Drive End Bearing	6312		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025