



Nameplate Specifications

Phase	3	Output HP	60 Hp
Output KW	44.8 kW	Voltage	230/460 V
Speed	1785 r/min	Service Factor	1.15
Frame	364T	Efficiency	93.6 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	144/72 A	Duty	Continuous
Insulation Class	F		

Technical Specifications

Rotation	Reversible Counterclockwise	Drive End Bearing	314
Opp Drive End Bearing	312		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025