

**Nameplate Specifications**

Phase	3	Output HP	60.0 Hp
Output KW	44.8 kW	Voltage	575 V
Speed	1780 r/min	Service Factor	1.15
Frame	364T	Enclosure	Totally Enclosed Non Ventilated
Efficiency	94.1 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	56 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

**Technical Specifications**

Poles	4	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	314sf
Opp Drive End Bearing	212sf	Frame Length	13.30 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025