



Nameplate Specifications

Phase	3	Output HP	100.0 Hp
Output KW	74.6 kW	Voltage	200 V
Speed	1785 r/min	Service Factor	1.15
Frame	Y404T	Efficiency	95.4 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	270 A	Duty	Continuous
Insulation Class	F		

Technical Specifications

Rotation	Reversible	Drive End Bearing	316
Opp Drive End Bearing	312		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025