

# PRODUCT INFORMATION PACKET



Model No: E757V1  
Catalog No: E757V1  
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

|                     |            |                |            |
|---------------------|------------|----------------|------------|
| Phase               | 3          | Output HP      | 150 Hp     |
| Output KW           | 111.9 kW   | Voltage        | 460 V      |
| Speed               | 3580 r/min | Service Factor | 1.15       |
| Frame               | 405TS      | Efficiency     | 94.1 %     |
| Ambient Temperature | 40 °C      | Frequency      | 60 Hz      |
| Current             | 162 A      | Duty           | Continuous |
| Insulation Class    | F          |                |            |

**Technical Specifications**

|                       |                             |                   |      |
|-----------------------|-----------------------------|-------------------|------|
| Rotation              | Reversible Counterclockwise | Drive End Bearing | 6312 |
| Opp Drive End Bearing | 6312                        |                   |      |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025