

**Nameplate Specifications**

Phase	1	Output HP	3.0 Hp
Output KW	2.2 kW	Voltage	115/230 V
Speed	1750 r/min	Service Factor	1.15
Frame	F184TC	Enclosure	Totally Enclosed Non Ventilated
Efficiency	76 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	34/17 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	4	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	206
Opp Drive End Bearing	204	Frame Length	7.20 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025