

Nameplate Specifications

Output HP	1/8-1/10-1/15-1/20 Hp	Output KW	0.10 kW
Frequency	60 Hz	Voltage	115 V
Current	2.3/1.6/1.2/0.7 A	Speed	1550 rpm
Service Factor	1	Phase	1
Duty	Continuous	Insulation Class	B
Frame	42None	Enclosure	Open Air Over
Thermal Protection	Automatic	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	4

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	4	Rotation	Clockwise Lead End
Mounting	Resilient Rings	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Na
Shaft Type	Flat	Overall Length	24.01 in
Shaft Diameter	0.500 in	Shaft Extension	10.50 in
Connection Drawing	SEE OUTLINE	Outline Drawing	7184001510_S001

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:08/24/2022