

# PRODUCT INFORMATION PACKET



Model No: 324TTTCD34601  
Catalog No: 324TTTCD34601  
20/15,900/750,TEAO,324TV,3/60/50/230/460#190/380

Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E






**Nameplate Specifications**

**Technical Specifications**


|                 |              |                    |        |
|-----------------|--------------|--------------------|--------|
| Shaft Diameter  | 2.125 in     |                    |        |
| Outline Drawing | SS620958-100 | Connection Drawing | EE7308 |

**This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/24/2023**


| 4        |       |       |      | 3     |       |       |      | 2    |          |          | 1 |
|----------|-------|-------|------|-------|-------|-------|------|------|----------|----------|---|
| DASH NO. | B     | C     | E    | 2E    | 2F    | 2FF   | BA   | BS   | MOUNTING | FRAME    |   |
| 100      | 12.71 | 26.37 | 6.25 | 12.50 | ---   | 10.50 | 5.25 | 5.25 | F1 OR F2 | 324T     |   |
| 200      | 14.21 | 27.87 |      |       | 10.50 | 12.00 |      | 6.00 |          | 324/326T |   |



1/2 x 1/2 x 3.88  
KEY




2" NPT  
LEAD HOLE



|  |                        |                               |
|--|------------------------|-------------------------------|
| DRAWING REVISION<br>B  | REVISION BY<br>ASHOK N | REV DATE/© DATE<br>04/11/2020 |
| ECO<br>ECO-0194180   | APPROVED BY<br>GNK     | DATE<br>04/11/2020            |
| ECO DESCRIPTION  |                        |                               |
| DRAWING UPDATED  |                        |                               |
| COPYRIGHT (PER REVISION DATE) REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS. |                        |                               |

PRIMARY DIMENSIONS ARE INCH  
mm DIMENSIONS IN [BRACKETS]  
ARE FOR REFERENCE ONLY

|                           |  |                            |
|---------------------------|--|----------------------------|
| DRAWN BY<br>SAI           |  Regal Beloit America, Inc. |                            |
| DATE<br>24/01/2020        |  |                            |
| APPROVED BY<br>SBD        | DESCRIPTION  |                            |
| DATE<br>24/01/2020        | OUTLINE  |                            |
| REFERENCE                 | MATERIAL   | PROCESS/FINISH             |
| THIRD ANGLE<br>PROJECTION | SIZE<br>B  | DRAWING NUMBER<br>SS620958 |
|                           |  | SHEET<br>1 OF 1            |



|   |  |                |         |                                |                 |   |          |                          |
|---|--|----------------|---------|--------------------------------|-----------------|---|----------|--------------------------|
|   |  |                |         | TOLERANCES<br>UNLESS SPECIFIED |                 |  <b>Regal Beloit America, Inc.</b> | DRAWN RM | 11/20/1990               |
| 5   | CHG TO REGAL LOGO                              | SL 09/10/2015  | AB      | DEC.                           | INCHES          |   | CHK ML   | 11/21/1990               |
| 4   | REVISED IEC NOTATIONS                          | MSG 11/15/2011 | CMN     | .X                             | ±.1             |   | APPD SAS | 04/24/2003               |
| 3   | ADDED IEC NOTATIONS... (U1), (V1) ETC. MU95194 | MSG 5/10/2010  | MJS     | .XX                            | ±.02            |   | SCALE    | 1=1                      |
| 2   | ADDED THE OPTIONAL CORD CONNECTION MU46318     | RDH 04/24/2003 | DRS     | .XXX                           | ±.005           | TITLE CONNECTION DIAGRAM<br>3Ø – DUAL VOLTAGE MOTOR   |          | REF                      |
| 1   | REDRAWN  | RM 11/20/1990  |         | .XXXX                          | ±.0005          | MAT'L.  |          | FMF                      |
| NO.   | REVISION                                       | BY & DATE      | CHK     | ANG                            | ±7"30"          | FINISH  |          | PREV                     |
| THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED<br>THIS IS AN ELECTRONICALLY GENERATED DOCUMENT – DO NOT SCALE THIS PRINT |  |                | RFP     |                                | CAD FILE ee7308 |   | SIZE     | DRAWING NO. PAGE OF REV. |
|   |  |                | DIST WP |                                | A               | EE7308  | 5        |                          |

THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT  
IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED  
THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT