

Nameplate Specifications

Output HP	100 Hp	Output KW	75.0 kW
Frequency	60 Hz	Voltage	575 V
Current	102.0 A	Speed	1768 rpm
Phase	3	Efficiency	92.9 %
Power Factor	79	Duty	NONE
Insulation Class	NONE	Design Code	NO DESIGN CODE
KVA Code	E	Frame	326TZ
Enclosure	PARTIAL	Thermal Protection	No Protection
Ambient Temperature	40 °C	Drive End Bearing Size	NONE
Opp Drive End Bearing Size	NONE	UL	No
CSA	Y	CE	Y
IP Code	43	Number of Speeds	1

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	NONE
Poles	4	Rotation	NONE
Resistance Main	.06 Ohms	Mounting	PARTIAL MOTOR
Motor Orientation	Horizontal	Frame Material	None
Shaft Type	Single Special Extension	Assembly/Box Mounting	F1/F2 CAPABLE
Connection Drawing	NONE	Outline Drawing	NONE

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/18/2022