

Nameplate Specifications

Output HP	5.0 Hp	Output KW	3.7 kW
Frequency	60 Hz	Voltage	575 V
Current	5.2 A	Speed	1740 rpm
Service Factor	1.15	Phase	3
Efficiency	87.5 %	Duty	Continuous
Insulation Class	F	Frame	184T
Thermal Protection	No Protection	Ambient Temperature	40 °C

Technical Specifications

Rotation	Reversible	Drive End Bearing	206
Opp Drive End Bearing	206		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:08/03/2022